





2022 USBC JUNIOR GOLD U18 U20 PATTERN #2



DISTANCE:	40 FEET	VOLUME:	26.85 mL
RATIO:	3.50:1	FORWARD:	16.45 mL
DROP BRUSH:	36 FEET	REVERSE:	10.4 mL
TANKS:	KEGEL	PUMP:	50µL



FORWARD LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	BUFF	TANK	DISTANCE	T.OIL
1	2L	2R	4	50	14	3	A - Kegel	0 → 6	7,400
2	2L	5R	1	50	18	3	A - Kegel	6 → 8	1,700
3	5L	7R	1	50	18	3	A - Kegel	8 → 11	1,450
4	9L	8R	1	50	18	3	A - Kegel	11 → 13	1,200
5	10L	9R	1	50	18	3	A - Kegel	13 → 16	1,100
6	11L	10R	1	50	18	3	A - Kegel	16 → 18	1,000
7	12L	11R	2	50	18	3	A - Kegel	18 → 24	1,800
8	13L	12R	1	50	18	3	A - Kegel	24 → 26	800
9	2L	2R	0	50	22	3	A - Kegel	26 → 36	0
10	2L	2R	0	50	26	3	A - Kegel	36 → 40	0

REVERSE LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	BUFF	TANK	DISTANCE	T.OIL
1	2L	2R	0	50	30	3	A - Kegel	36 → 30	0
2	12L	12R	2	50	18	3	A - Kegel	30 → 25	1,700
3	11L	11R	1	50	18	3	A - Kegel	25 → 22	950
4	10L	10R	2	50	18	3	A - Kegel	22 → 17	2,100
5	9L	9R	1	50	18	3	A - Kegel	17 → 15	1,150
6	8L	8R	1	50	18	3	A - Kegel	15 → 12	1,250
7	6L	7R	1	50	18	3	A - Kegel	12 → 10	1,400
8	2L	2R	1	50	18	3	A - Kegel	10 → 7	1,850
9	2L	2R	0	50	14	3	A - Kegel	7 → 0	0

THIS PATTERN IS DESIGNED FOR:
REVERSE DROP BRUSH

This pattern may require adjustments if using a lane machine that does not have these features



KEGEL PATTERN LIBRARY APP



PATTERNLIBRARY.KEGEL.NET



SCAN QR CODE TO
SHARE AND
DOWNLOAD
THIS PATTERN

